

TSL-3002

Hand Dryer

The Splash Lab TSL-3002 is a slim-line high speed hand dryer with the advantage of a 15 second drying time and low running costs.



CODES	VOLTAGE	FREQUENCY	CURRENT OUTLET	AIR TEMPERATURE
TSL-3002	220-240V	50Hz	4.2A	55°C / 131°F
TECHNICAL DATA			LIGHT REFLECTION VALUES	
Finishes	CS (Brushed satin stainless steel)			58
	CP (Brushed copper finish)			19
	BK (Brushed black finish)			3
	BZ (Brushed bronze finish)			17
	BR (Brushed brass finish)			40
Power Consumption	4.2A			
Drying time	less than 15 seconds			
Weight	4.9kg			
Stainless steel	AISI 304			
Noise levels	Min 69dB to 76.6dB Max @ 1 metre			
Air speed	95-115m/s			
Heating element	450W adjustable			
Motor type	Brush type, Dual ball-bearings			
Motor power	250W – 500W			
Motor	16,000 – 29,000 RPM variable speed			
Air Flow	74m³/h			
Sensor range	100 – 230mm variable; standard set at 17cm			
Approvals	CE, UL, RoHS			
Insulation	Class 1			
IP rating	IP24			
Warranty	1 year parts and labour; additional 4 years parts-only. (Motor brushes excluded as these are a wearing part, and dependent on usage.)			

---

## INSTALLATION GUIDELINES

---

Installation height	(All dimensions taken from finished floor level to base of hand dryer) Male washroom 1220mm Female washroom 1120mm Primary school washroom 910mm Wheelchair accessible 910mm
Washroom layout	<p>Number of hand dryers to be fitted – for toilet areas with normal frequency; one dryer per two washbasins. In high-frequency use toilet areas; two dryers per 3 basins. In very high frequency use washrooms, one dryer per basin. Mounting template included with dryer.</p> <p>Ideal location – between washbasin and exit. If mounted over a washbasin, recommended minimum distance from dryer to basin should be 300mm.</p> <p>Dryer can be installed behind a mirror or cabinet, but must be accessible for maintenance. In this application, the dryer must be mounted with the base flush with the base of the mirror or cabinet so that the sensor is not obstructed.</p> <p>Recommended mounting substrate is a solid wall. If dryer is installed on a stud / plasterboard wall, sound levels are likely to exceed 78dB.</p>

---

## COMPLIANCE

---

CE

RoHS

UL

---


## RELATED DOCUMENTS

---


Installation and maintenance manual	email: <a href="mailto:technical@thesplashlab.com">technical@thesplashlab.com</a>
Warranty document	email: <a href="mailto:technical@thesplashlab.com">technical@thesplashlab.com</a>

## TECHNICAL DRAWING



FRONT



SIDE



FIXING



### Recommended install height (UK)

Mens Washroom	-1220mm
Ladies Washroom	-1120mm
School Washroom	-910mm
Disabled Washroom	-910mm